



Revision Number: 003.0

Issue date: 08/30/2017

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE 567 TB 50ML EN	IDH number:	2087067
Product type:	Anaerobic Sealant	Item number:	2087067
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: +1 (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: CAUSES SKIN IRRITATION.
MAY CAUSE AN ALLERGIC SKIN REACTION.
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Avoid breathing vapors, mist, or spray. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
Response:	IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
Storage:	Not prescribed
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
------------------------	------------	-------------

3,3,5 Trimethylcyclohexyl methacrylate	7779-31-9	20 - 30
Ethene, homopolymer	9002-88-4	5 - 10
Ethene, tetrafluoro-, homopolymer	9002-84-0	5 - 10
Titanium dioxide	13463-67-7	1 - 5
Silica, amorphous, fumed, crystal-free	112945-52-5	1 - 5
Propane-1,2-diol	57-55-6	1 - 5
Cumene hydroperoxide	80-15-9	0.1 - 1
Cumene	98-82-8	0.1 - 1

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Not available.
Skin contact:	Not available.
Eye contact:	Not available.
Ingestion:	Not available.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
Unusual fire or explosion hazards:	Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers.
Hazardous combustion products:	Oxides of carbon and nitrogen, aldehydes, acids and undetermined organics. Toxic fluorine compounds. Ketones.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

Handling:	Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. Refer to Section 8.
Storage:	Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
3,3,5 Trimethylcyclohexyl methacrylate	None	None	None	None
Ethene, homopolymer	10 mg/m3 TWA Inhalable particles. 3 mg/m3 TWA Respirable particles.	15 MPPCF TWA Respirable fraction. 15 mg/m3 TWA Total dust. 50 MPPCF TWA Total dust. 5 mg/m3 TWA Respirable fraction. 5 mg/m3 PEL Respirable fraction. 15 mg/m3 PEL Total dust.	None	None
Ethene, tetrafluoro-, homopolymer	None	None	None	10 mg/m3 TWA Total dust. 5 mg/m3 TWA Respirable fraction.
Titanium dioxide	10 mg/m3 TWA	15 mg/m3 PEL Total dust. 15 MPPCF TWA Respirable fraction. 15 mg/m3 TWA Total dust. 50 MPPCF TWA Total dust. 5 mg/m3 TWA Respirable fraction.	None	None
Silica, amorphous, fumed, crystal-free	10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction.	20 MPPCF TWA 0.8 mg/m3 TWA	None	None
Propane-1,2-diol	None	None	10 mg/m3 TWA Aerosol.	None
Cumene hydroperoxide	None	None	1 ppm (6 mg/m3) TWA (SKIN)	None
Cumene	50 ppm TWA	50 ppm (245 mg/m3) PEL (SKIN)	None	None

Engineering controls:

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection:

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection:

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection:

Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Paste, Liquid
Color:	Off white
Odor:	Mild
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	Not available.
Boiling point/range:	> 149 °C (> 300.2 °F)no method
Melting point/ range:	Not available.
Specific gravity:	1.15
Vapor density:	Not available.
Flash point:	> 93 °C (> 199.4 °F)
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Not available.
Partition coefficient (n-octanol/water):	Not available.
VOC content:	0.13 % (ASTM D5403)
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing. Polymerization may occur at elevated temperature or in the presence of incompatible materials.
Hazardous decomposition products:	Oxides of carbon and nitrogen, aldehydes, acids and undetermined organics. Toxic fluorine compounds. Ketones.
Incompatible materials:	Strong oxidizing agents. Strong reducing agents. Free radical initiators. Inert gases. Oxygen scavengers.
Reactivity:	Not available.
Conditions to avoid:	Elevated temperatures. Heat, flames, sparks and other sources of ignition. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure:	Skin, Inhalation, Eyes, Ingestion
------------------------------	-----------------------------------

Potential Health Effects/Symptoms

Inhalation:	Inhalation of vapors or mists of the product may be irritating to the respiratory system.
Skin contact:	Causes skin irritation. May cause allergic skin reaction.
Eye contact:	Causes serious eye irritation.
Ingestion:	May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
3,3,5 Trimethylcyclohexyl methacrylate	None	No Records
Ethene, homopolymer	None	No Target Organs
Ethene, tetrafluoro-, homopolymer	None	No Target Organs
Titanium dioxide	None	Irritant, Respiratory, Some evidence of carcinogenicity
Silica, amorphous, fumed, crystal-free	None	Nuisance dust
Propane-1,2-diol	Oral LD50 (Rabbit) = 18 g/kg Oral LD50 (Mouse) = 23.9 g/kg Oral LD50 (Rat) = 30 g/kg	Irritant
Cumene hydroperoxide	Inhalation LC50 (Mouse, 4 h) = 200 mg/l	Allergen, Central nervous system, Corrosive, Irritant, Mutagen
Cumene	Oral LD50 (Rat) = 2.91 g/kg Oral LD50 (Rat) = 1,400 mg/kg Inhalation LC50 (Rat, 4 h) = 8000 ppm	Central nervous system, Irritant, Lung

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
3,3,5 Trimethylcyclohexyl methacrylate	No	No	No
Ethene, homopolymer	No	No	No
Ethene, tetrafluoro-, homopolymer	No	No	No
Titanium dioxide	No	Group 2B	No
Silica, amorphous, fumed, crystal-free	No	No	No
Propane-1,2-diol	No	No	No
Cumene hydroperoxide	No	No	No
Cumene	Reasonably Anticipated to be a Human Carcinogen.	Group 2B	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name:	RQ, Environmentally hazardous substance, liquid, n.o.s.
Hazard class or division:	9
Identification number:	UN 3082
Packing group:	III
DOT Hazardous Substance(s):	alpha,alpha-Dimethylbenzylhydroperoxide

International Air Transportation (ICAO/IATA)

Proper shipping name: RQ, Environmentally hazardous substance, liquid, n.o.s.
Hazard class or division: 9
Identification number: UN 3082
Packing group: III

Water Transportation (IMO/IMDG)

Proper shipping name: RQ, ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
Hazard class or division: 9
Identification number: UN 3082
Packing group: III

15. REGULATORY INFORMATION**United States Regulatory Information**

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: Ethene, tetrafluoro-, homopolymer (CAS# 9002-84-0).
CERCLA/SARA Section 302 EHS: None above reporting de minimis.
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health
CERCLA/SARA Section 313: None above reporting de minimis.
CERCLA Reportable quantity: Cumene hydroperoxide (CAS# 80-15-9) 10 lbs. (4.54 kg)
California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: One or more components are not listed on, and are not exempt from listing on either the Domestic Substances List or the Non-Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: 2

Prepared by: Sheila Gines, Regulatory Affairs Specialist

Issue date: 08/30/2017

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.