

Safety Data Sheet

acc. to OSHA HCS

Printing date 04/18/2017

Reviewed on 04/18/2017

1 Identification

- **Product identifier**
- **Trade name:** Freedom Form Release
- **Article number:** 83-140638
- **Application of the substance / the mixture**
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Fastenal
2001 Theurer Blvd.
Winona, MN. 55987

Tel.: (507) 454-5374

Emergency Telephone Number: Use only in the event of an emergency involving a spill, leak, fire, exposure, or accident involving chemicals. Within the U.S., Canada, or the U.S. Virgin Islands, call ChemTrec at (800) 424-9300, 24 hours a day.

- **Information department:** Environmental, Health, and Safety department.

2 Hazard(s) identification

- **Classification of the substance or mixture**
STOT SE 3 H335 May cause respiratory irritation.
- **Label elements**
- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS07

- **Signal word** Warning
- **Hazard-determining components of labeling:**
Distillates (petroleum), hydrotreated light naphthenic
- **Hazard statements**
May cause respiratory irritation.
- **Precautionary statements**
Avoid breathing dust/fume/gas/mist/vapors/spray
IF INHALED: Remove person to fresh air and keep comfortable for breathing.
Call a POISON CENTER/doctor if you feel unwell.
Store locked up.
Store in a well-ventilated place. Keep container tightly closed.
Dispose of contents/container in accordance with local/regional/national/international regulations.
- **Classification system:**
- **NFPA ratings (scale 0 - 4)**



Health = 1
Fire = 1
Reactivity = 0

- **HMIS-ratings (scale 0 - 4)**

HEALTH	1
FIRE	1
PHYSICAL HAZARD	0

Health = 1
Fire = 1
Reactivity = 0

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 04/18/2017

Reviewed on 04/18/2017

Trade name: Freedom Form Release

(Contd. of page 1)

- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization: Mixtures**
- **Description:** Mixture of the substances listed below with nonhazardous additions.

- **Dangerous components:**

64742-53-6	Distillates (petroleum), hydrotreated light naphthenic	50-75%
64742-65-0	Distillates (petroleum), solvent-dewaxed heavy paraffinic	10-25%
64742-57-0	Residual oils (petroleum), hydrotreated	≤ 10%
64742-62-7	Residual oils (petroleum), solvent-dewaxed	≤ 10%
61790-12-3	Distilled Tall Oil Fatty Acids	≤ 5%

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

4 First-aid measures

- **Description of first aid measures**
- **General information:**
Immediately remove any clothing soiled by the product.
In the event of persistent symptoms receive medical treatment.
- **After inhalation:**
Supply fresh air and to be sure call for a doctor.
In case of unconsciousness place patient stably in side position for transportation.
Immediately move exposed person to fresh air. If breathing difficulty persists or develops get prompt medical attention.
- **After skin contact:**
Immediately wash with water and soap and rinse thoroughly.
Immediately rinse with water.
If skin irritation continues, consult a doctor.
- **After eye contact:** Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Seek medical treatment.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed** No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:**
Because fire may produce thermal decomposition products, wear a self-contained breathing apparatus (SCBA) with a full face piece operated in pressure-demand or positive-pressure mode.

US

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 04/18/2017

Reviewed on 04/18/2017

Trade name: Freedom Form Release

(Contd. of page 2)

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**

Wear protective equipment. Keep unprotected persons away.

- **Environmental precautions:**

Do not allow product to reach sewage system or any water course.

Inform respective authorities in case of seepage into water course or sewage system.

- **Methods and material for containment and cleaning up:**

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Dispose contaminated material as waste according to item 13.

Ensure adequate ventilation.

- **Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

- **Protective Action Criteria for Chemicals**

- **PAC-1:**

64742-65-0	Distillates (petroleum), solvent-dewaxed heavy paraffinic	140 mg/m ³
111-42-2	2,2'-iminodiethanol	3 mg/m ³

- **PAC-2:**

64742-65-0	Distillates (petroleum), solvent-dewaxed heavy paraffinic	1,500 mg/m ³
111-42-2	2,2'-iminodiethanol	28 mg/m ³

- **PAC-3:**

64742-65-0	Distillates (petroleum), solvent-dewaxed heavy paraffinic	8,900 mg/m ³
111-42-2	2,2'-iminodiethanol	130 mg/m ³

7 Handling and storage

- **Handling:**

- **Precautions for safe handling**

Wear appropriate personal protective clothing to prevent eye and skin contact. Avoid breathing vapors or mists of this product. Use with adequate ventilation. Do not take internally.

- **Information about protection against explosions and fires:** Keep respiratory protective device available.

- **Conditions for safe storage, including any incompatibilities**

· **Storage:** cool and dry

· **Requirements to be met by storerooms and receptacles:** No special requirements.

· **Information about storage in one common storage facility:** Not required.

· **Further information about storage conditions:** Keep receptacle tightly sealed.

· **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

· **Additional information about design of technical systems:** No further data; see item 7.

- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· **Additional information:** The lists that were valid during the creation were used as basis.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 04/18/2017

Reviewed on 04/18/2017

Trade name: Freedom Form Release

(Contd. of page 3)

· **Exposure controls**· **Personal protective equipment:**· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Avoid contact with the eyes and skin.

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**

Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

· **Eye protection:** Wear appropriate eye protection to prevent eye contact.

9 Physical and chemical properties

· **Information on basic physical and chemical properties**· **General Information**· **Appearance:****Form:**

Liquid

Color:

According to product specification

· **Odor:**

Characteristic

· **Odor threshold:**

Not determined.

· **pH-value:**

Not determined.

· **Change in condition****Melting point/Melting range:**

Undetermined.

Boiling point/Boiling range:

>218 °C (>424 °F)

· **Flash point:**

140 °C (284 °F)

· **Flammability (solid, gaseous):**

Not applicable.

· **Ignition temperature:**

307 °C (585 °F)

· **Decomposition temperature:**

Not determined.

· **Auto igniting:**

Product is not selfigniting.

· **Danger of explosion:**

Product does not present an explosion hazard.

· **Explosion limits:****Lower:**

Not determined.

Upper:

Not determined.

· **Vapor pressure:**

Not determined.

· **Density at 20 °C (68 °F):**0.861 g/cm³ (7.185 lbs/gal)· **Relative density**

Not determined.

· **Vapor density**

Not determined.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 04/18/2017

Reviewed on 04/18/2017

Trade name: Freedom Form Release

(Contd. of page 4)

· Evaporation rate	Not determined.
· Solubility in / Miscibility with Water:	Not miscible or difficult to mix.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic at 20 °C (68 °F):	0 mPas
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	0.0 %
Solids content:	72.5 %
· Other information	No further relevant information available.
· Volatile Organic Compounds:	Contains less than 250 g/L.

10 Stability and reactivity

- **Reactivity** No decomposition if stored and applied as directed.
- **Chemical stability** No decomposition if stored and applied as directed
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** Keep away from heat and sources of ignition.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect known.
- **on the eye:** No irritating effect known.
- **Sensitization:** Sensitization possible through skin contact.
- **Additional toxicological information:**
The product shows the following dangers according to internally approved calculation methods for preparations:
Irritant
Carcinogenic.
- **Carcinogenic categories**

· IARC (International Agency for Research on Cancer)

111-42-2 | 2,2'-iminodiethanol

2B

· NTP (National Toxicology Program)

None of the ingredients is listed.

· OSHA-Ca (Occupational Safety & Health Administration)

None of the ingredients is listed.

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 04/18/2017

Reviewed on 04/18/2017

Trade name: Freedom Form Release

(Contd. of page 5)

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Water hazard class 1 (Self-assessment): slightly hazardous for water
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
It is the generator's responsibility to determine if the waste meets applicable definitions of hazardous waste. State and local regulations may differ from federal disposal regulations. Dispose of waste material according to local, state, federal, and provincial environmental regulations.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to Federal, State, and Local regulations.

14 Transport information

- | | |
|---|--|
| · UN-Number | |
| · DOT, ADR, ADN, IMDG, IATA | Not Regulated |
| · UN proper shipping name | |
| · DOT, ADR, ADN, IMDG, IATA | Not Regulated |
| · Transport hazard class(es) | |
| · DOT, ADR, ADN, IMDG, IATA | |
| · Class | Not Regulated |
| · Packing group | |
| · DOT, ADR, IMDG, IATA | Not Regulated |
| · Environmental hazards: | |
| · Marine pollutant: | No |
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |
| · Transport/Additional information: | |
| · ADR | |
| · U.S. Domestic Ground Shipments: | Not Regulated by D.O.T. |
| · U.S. Domestic Ground Non-Bulk (119 gal or less per container) Shipments: | Same as listed for Standard Shipments above. |
| · Emergency Response Guide (ERG) Number: | Not determine |

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 04/18/2017

Reviewed on 04/18/2017

Trade name: Freedom Form Release

(Contd. of page 6)

· UN "Model Regulation":

Not Regulated

15 Regulatory information

- Safety, health and environmental regulations/legislation specific for the substance or mixture
- Sara

· Section 355 (extremely hazardous substances):

None of the ingredient is listed.

· Section 313 (Specific toxic chemical listings):

This product may contain 1 or more toxic chemicals subject to the reporting requirements of Section 313 of Title III of the Superfund Amendments and Reauthorization Act (SARA) of 1986 and 40 CFR part 372. If so, the chemicals are listed below.

111-42-2	2,2'-iminodiethanol	≤0.1%
----------	---------------------	-------

· TSCA (Toxic Substances Control Act):

64742-53-6	Distillates (petroleum), hydrotreated light naphthenic
64742-65-0	Distillates (petroleum), solvent-dewaxed heavy paraffinic
64742-57-0	Residual oils (petroleum), hydrotreated
72623-83-7	Lubricating oils, petroleum
64742-62-7	Residual oils (petroleum), solvent-dewaxed
61790-12-3	Distilled Tall Oil Fatty Acids
8051-30-7	Coconut oil, reaction products with diethanolamine
111-42-2	2,2'-iminodiethanol

· Proposition 65

· Chemicals known to the State of California (Prop. 65) to cause cancer:

111-42-2	2,2'-iminodiethanol
----------	---------------------

· Chemicals known to cause reproductive toxicity for females:

None of the ingredients is listed.

· Chemicals known to cause reproductive toxicity for males:

None of the ingredients is listed.

· Chemicals known to cause developmental toxicity:

None of the ingredients is listed.

· Cancerogenity categories

· EPA (Environmental Protection Agency)

None of the ingredients is listed.

· TLV (Threshold Limit Value established by ACGIH)

111-42-2	2,2'-iminodiethanol	A3
----------	---------------------	----

· MAK (German Maximum Workplace Concentration)

111-42-2	2,2'-iminodiethanol	3B
----------	---------------------	----

· NIOSH-Ca (National Institute for Occupational Safety and Health)

None of the ingredients is listed.

- GHS label elements The product is classified and labeled according to the Globally Harmonized System (GHS).

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 04/18/2017

Reviewed on 04/18/2017

Trade name: Freedom Form Release

(Contd. of page 7)

· **Hazard pictograms**

GHS07

· **Signal word** Warning· **Hazard-determining components of labeling:**

Distillates (petroleum), hydrotreated light naphthenic

· **Hazard statements**

May cause respiratory irritation.

· **Precautionary statements**

Avoid breathing dust/fume/gas/mist/vapors/spray

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Call a POISON CENTER/doctor if you feel unwell.

Store locked up.

Store in a well-ventilated place. Keep container tightly closed.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **National regulations:**· **Information about limitation of use:**

Workers are not allowed to be exposed to the hazardous carcinogenic materials contained in this preparation. Exceptions can be made by the authorities in certain cases.

· **Water hazard class:** Water hazard class 3 (Self-assessment): extremely hazardous for water.· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environmental, Health & Safety Department· **Contact:** Environmental, Health & Safety Manager· **Date of preparation / last revision** 04/18/2017 / 147· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3